



UNDERCABINET LINEAFLEX SENSOR




	EAN	W	lm light source	lm output	K	Temp. (°C)	V~	mA	Hz	DF	PF	∠ (°)	
UCABINET LINEAFLEX 360 5.3WCCTDIMST	4099854628160	5.3	500	380	2700/ 4000	-20... +40	220- 240	48	50/ 60	≥0.5	≥0.5	120	10000
UCABINET LINEAFLEX 360 4.2WCCTDIMEX	4099854628184	4.2	500	380	2700/ 4000	-20... +40	DC24V	175	-	-	1	120	10000
UCABINET LINEAFLEX 540 8.5WCCTDIMST	4099854628207	8.5	850	620	2700/ 4000	-20... +40	220- 240	68	50/ 60	≥0.5	≥0.5	120	10000
UCABINET LINEAFLEX 540 7W CCT DIMEX	4099854628221	7	850	620	2700/ 4000	-20... +40	DC24V	292	-	-	1	120	10000
UCABINET LINEAFLEX COR 0.88W CCTDIM	4099854628245	0.88	106	40	2700/ 4000	-20... +40	DC24V	37	-	-	1	120	10000


UNDERCABINET LINEAFLEX SENSOR






Starterkit


1x  **395 g**
4099854628160

1.5m



1x  **550 g**
4099854628207


2x  **4099854628160**



1x  1x  **3x 4099854628207**

1x  **310 g**
4099854628184


0.2m

1x  2x  **470 g**
4099854628221


3x  **4099854628221**

1x  1x  **55 g**
4099854628245


mm



	L	W	H
4099854628160	360	90	12
4099854628184	360	90	12
4099854628207	540	90	12
4099854628221	540	90	12
4099854628245	90	90	12




EAN
4099854628184
4099854628221





EAN
4099854628245

You need a basic product (not included) to use the extension**


1



UNDERCABINET LINEAFLEX SENSOR







OR





UNDERCABINET LINEAFLEX SENSOR





5



6



UNDERCABINET LINEAFLEX SENSOR



	EAN	n		QR code	ENERGY * X =
UCABINET LINEAFLEX 360 5.3WCCTDIMST	4099854628160	1	AC83842		E
UCABINET LINEAFLEX 360 4.2WCCTDIMEX	4099854628184	1	AC83842		E
UCABINET LINEAFLEX 540 8.5WCCTDIMST	4099854628207	1	AC83843		E
UCABINET LINEAFLEX 540 7W CCT DIMEX	4099854628221	1	AC83843		E
UCABINET LINEAFLEX COR 0.88W CCTDIM	4099854628245	1	AC83844		E

** ☺ Referenzkontrolleinstellung ☺ Réglage de la commande de référence ☺ Impostazione controllo di riferimento ☺ Configuración de control de referencia ☺ Configuração de controlo de referência ☺ Ρύθμιση χειρισμού αναφοράς ☺ Referenzbesturingsinstelling ☺ Inställning för referenskontroll ☺ Vertailuasetus ☺ Referansekontrollininstilling ☺ Referençekontrolindstilling ☺ Nastavení referenčního ovládání ☺ Referencia vezérlés beállítás ☺ Ustawienie kontroli wartości odniesienia ☺ Nastawienie referençnego ovládania ☺ Nastawitev referençnega nadzora ☺ Referans kontrol ayarı ☺ Referentna kontrolna postavka ☺ Setare control de referință ☺ Настройка на референция контрол ☺ Võrdluskontrolli seadistus ☺ Etaloninio valdymo nustatymas ☺ Atsauces vadības iestatījums ☺ Postavka kontrole referençe ☺ Налаштування еталонного контролю

